

Contents in this document may change without prior notice.
Please obtain the delivery specification for the latest design.



EM Series Gesture Model
7" Wide Embedded Panel Computer

EMG7

Model: EMG7-W207A8-0024-107-01

Product Specification

DMC Co., Ltd.
<https://www.dush.co.jp/english/>

Table of Contents

| | |
|---|----|
| 1. Summary | 3 |
| 2. Product Model | 3 |
| 3. Packaged Contents | 3 |
| 4. Specification | 4 |
| 4-1 Functional specification | 4 |
| 4-2 Display Specifications | 5 |
| 4-3 Touch Screen Specification | 5 |
| 4-4 General Specification | 5 |
| 4-5 Environmental Specification | 6 |
| 4-6 Installation Specification | 6 |
| 4-7 Names of Parts | 7 |
| 4-7-1 Front | 7 |
| 4-7-2 Back | 7 |
| 4-7-3 Right | 8 |
| 4-7-4 Top | 8 |
| 4-7-5 Bottom | 8 |
| 4-8 External Interface | 9 |
| 4-8-1 SD Card Slot | 9 |
| 4-8-2 Serial Port (COM 1) | 9 |
| 4-8-3 Ethernet | 9 |
| 4-8-4 USB Host Port | 10 |
| 4-8-5 USB Device Port | 10 |
| 4-8-6 Audio Interface (LINE OUT) | 11 |
| 4-8-7 Audio Interface (MIC IN) | 11 |
| 4-8-8 Power Connector | 11 |
| 4-9 Software Specification | 12 |
| 4-9-1 Embedded Linux | 12 |
| 5. Installation | 13 |
| 5-1 Installing Condition | 13 |
| 5-2 Mounting | 14 |
| 5-2-1 Panel Mounting | 14 |
| 5-2-2 Mounting to a VESA Arm | 15 |
| 6. Compatible Standards | 16 |
| 6-1 UL Standard | 16 |
| 6-2 CE Marking | 16 |
| 6-3 RoHS Directives | 16 |
| 6-4 FCC | 16 |
| 7. List of Option | 17 |
| 8. Warranty | 18 |
| 8-1 Warranty Period | 18 |
| 8-2 Warranty Exceptions | 18 |
| 9. Production Discontinuance | 18 |
| 10. Others | 19 |
| Appendix: Outline drawing (SM3-001905-11) | |

1. Summary

This specification describes the 7"W LCD projected capacitive panel computer.

OS line up is Embedded Linux.

The panel computer will be referred to as EMG7 hereinafter.

2. Product Model

| Specification | Model |
|-------------------------------|-------------------------|
| Embedded Linux Panel computer | EMG7-W207A8-0024-107-01 |

3. Packaged Contents

The following items are included in the package:

- EMG7 1 unit
- Mounting Bracket (IS-TK-01) 1 set (4 pcs)
- Battery 1 pc
- Protective Sheet 1 pc
- Gasket 1 pc (Pre-installed to unit)
- Power Connector 1 pc
- Serial Port Connector 1 pc
- Installation Guide 2 pcs(1 English version and 1 Japanese version.)
- Packaging List 2 pcs(1 English version and 1 Japanese version.)

4. Specification

4-1 Functional specification

| Item | | Specifications | |
|---------------------|--|--|--|
| CPU | | NXP i.MX535 1GHz | |
| RAM | | DDR3-SDRAM 512MB | |
| ROM | | NAND Flash 512MB | |
| Battery Backup SRAM | | 512KB | |
| Interface | Serial | RS232C (COM1) : x 1 (5-pin connector) | |
| | Ethernet | 10BASE-T/100BASE-TX : x 1 | |
| | SD Card *1 | SD/SDHC card slot : x 1 | |
| | USB Host *2 | USB2.0 : x 2 (TYPE-A connector) | |
| | | USB devices that can be used : keyboard, mouse (HID Class), USB memory (Mass Storage Class) | |
| | USB Device *3 | USB2.0 : x 1 (mini TYPE-B connector) | |
| | Audio | Line Output : x 1 (φ3.5 JACK) | |
| | | MIC Input : x 1 (φ3.5 JACK) | |
| Buzzer | On-board Buzzer | | |
| RTC*4 | RTC with a battery backup Error at the time of backup :±65 seconds/month (Conditions: ambient temperature 25 °C) | | |

*1. Does not guarantee accurate operation for all SD memory cards available in the market.

*2. Does not guarantee accurate function for all USB devices available in the market.

*3. Embedded Linux version EMG 7 is recognized as USB Mass Storage class.

*4. Above chart shows RTC with battery back-up embedded on the EMG7.

EMG7 normally uses timer inside of the CPU for time display. If time according to specification is needed, please refer to RTC built-in the EMG7.

When using in system where time error becomes a problem, please set to correct time on a regular basis.

4-2 Display Specifications

| Item | | Specifications |
|---------|-----------------------------------|-------------------------|
| Display | Type | 7-inch Wide TFT LCD |
| | Resolution | 800(W) X 480(H) |
| | Color | 65,536 colors |
| | Backlight | LED (not replaceable) |
| | Brightness | 310 cd/m ² |
| | Backlight brightness adjustment*1 | Adjustable in 16 levels |
| | Backlight life *2 | 70,000 hours average |

*1. 4 levels of adjustment are possible by the EMG tool.

*2. Time until brightness declines by 50% from the initial value at maximum brightness in ambient temperature of 25°C.

4-3 Touch Screen Specification

| Item | Specifications |
|----------------|---|
| Type | Projected capacitive |
| Input Type | Finger |
| Multi-touch | Two points *1 |
| Operating life | Continuous typing (finger input):50 million times |

*1. Application for two points simultaneous input must be created by customer.

Note: Touch screen operations will become unstable depending on the installation environment due to its characteristics. In order to use it correctly, perform calibration for sensitivity sensor of touch screen when building into a device.

Also, if at any time the touch screen operations become unstable due to changes in the setting environment or installation, perform sensitivity sensor calibration.

If there is moisture on the touch screen surface, it may not operate properly.

When moisture there is on the surface, please wipe it dry before use.

4-4 General Specification

| Item | | Specifications |
|-------|-------------------|---|
| Power | Rated voltage | 24VDC |
| | Voltage tolerance | 24VDC ± 20% |
| | Power consumption | 15W or under (Typ. 7W) *1 |
| | FG Connection | FG (Frame GND) and SG (Signal GND) are connected internally. FG (Frame GND) and GND are not connected. |

*1. Power consumption of the unit only. Please consider the power consumption of the USB device when using the USB.

Note: When gentle power source is used for rising and falling of power, it may not operate properly.

Also, when rebooting EMG7, leave it off for a while after turning off; do not turn the power back on immediately. It may not start up accurately.

4-5 Environmental Specification

| Item | Specifications |
|--|---|
| Ambient operating temperature (Inside cabinet and display side) | 0°C to 55°C |
| Ambient storage temperature | -10°C to +60°C |
| Ambient operating humidity | 10%RH to 85%RH (non-condensing. Wet-bulb temperature is 39 °C or less) |
| Ambient storage humidity | 10%RH to 85%RH (non-condensing. Wet-bulb temperature is 39 °C or less) |
| Dust | Prohibited |
| Corrosive Gas | Corrosive gas Prohibited |
| Environment | Pollution Degree 2, Indoor use |
| Pressure resistance | 800hPa to 1114hPa (Altitude up to 2000m) |
| Vibration resistance | IEC61131-2(JIS B 3502) compliant 5Hz to 9Hz Single amplitude 3.5mm 9Hz to 150Hz Fixed acceleration 9.8m/s ² X,Y,Z directions for 10times(100min.) |


4-6 Installation Specification

| Item | Specifications |
|-------------------------|---|
| Grounding | Grounding resistance of 100Ω, 2mm ² [0.0062inch ²] or thicker wire, or your country's applicable standard. |
| Structure | Protection Structure: IP65 *1 (Front side only when mounted to panel) Installation: Panel mounting |
| Cooling | Natural cooling |
| Weight | Approx. 700g (unit only) |
| External Dimensions | 192 (W) mm x 137 (H) mm x 36 (D) mm |
| Panel Cutout Dimensions | 183.5 ^{+0.5/-0} (W) mm x 128.5 ^{+0.5/-0} (H) mm |
| Color | Black |

- *1. Protection structure of the front part of the unit when installed to a panel. Although it has been tested under conditions equivalent to the standards shown in the specification, use under all environments are not guaranteed. Especially for oils defined in the test, in cases where EMG7 is prolonged to vaporized oils or cutting fluids with especially low viscosity, oil might enter the front area through an area where touch screen has lifted and may need special measurements. Please check the installation environment prior to use. Also, gaskets that have been used for a long time or have once been installed to panels, the original level of the protection cannot be guaranteed. To maintain the stable, original protection level, we recommend replacing the installation gasket regularly.

4-7 Names of Parts

4-7-1 Front




A) Status LED

The status LED displays the state of the EMG by the LED color shown below:


| LED State | EMG State |
|-----------------|-------------------------------------|
| Off | Power not applied |
| Amber, steady | OS starting |
| Green, steady | Normal operating state |
| Green, blinking | Backlight off (Normal Operation) |

4-7-2 Back



- B) Battery cover
- C) Product label
- D) FCC label

4-7-3 Right




- E) SD Card Slot
- F) USB Device
- G) Audio Interface (LINE OUT)
- H) Audio Interface (MIC IN)

4-7-4 Top



- I) Mounting Holes

4-7-5 Bottom



- J) Power Input
- K) Ethernet
- L) USB Host
- M) Serial Port (COM1)
- N) Mounting Holes

4-8 External Interface

4-8-1 SD Card Slot

Connector : SD / SDHC memory card (Push-in/push-out method)
 Corresponding media : SD/SDHC memory card
 Maximum capacity : 32GB

4-8-2 Serial Port (COM 1)

Serial port : RS232C
 Connector : Euro terminal connector (<Tyco Electronics> 284539-5)
 Recommended cable connector : (<Tyco Electronics>284510-5) *Included as accessory.

| PIN No. | Signal | Schematic |
|---------|--------|-----------|
| 1 | TXD | |
| 2 | RXD | |
| 3 | RTS | |
| 4 | CTS | |
| 5 | SG | |

4-8-3 Ethernet

Ethernet : 10BASE-T/100BASE-TX
 Connector : RJ-45

| PIN No. | Signal | Schematic |
|---------|--------|-----------|
| 1 | TX+ | |
| 2 | TX- | |
| 3 | RX+ | |
| 4 | NC *1 | |
| 5 | NC *1 | |
| 6 | RX- | |
| 7 | NC *1 | |
| 8 | NC *1 | |

*1. NC is 'not connected'.


Status LED

| LED State | State |
|------------|----------|
| On, Green | LINK/ACT |
| On, Yellow | SPEED |

Compatible cable : Above category 5


4-8-4 USB Host Port

Interface : USB2.0
 Number of Ports : 2
 Connector : Type-A connector
 Maximum supply current: 0.5A / Port

| PIN No. | Signal (All ports common) | Schematic |
|---------|------------------------------|--|
| 1 | USB_VCC |  |
| 2 | D- | |
| 3 | D+ | |
| 4 | SG | |
| | | |

4-8-5 USB Device Port

Interface : USB2.0
 Connector : Type-B Mini connector

| PIN No. | Signal | Schematic |
|---------|---------|--|
| 1 | USB_VCC |  |
| 2 | D- | |
| 3 | D+ | |
| 4 | NC *1 | |
| 5 | SG | |

*1. NC is 'not connected'.

4-8-6 Audio Interface (LINE OUT)

Interface : LINE OUT (Stereo)

Connector : ϕ 3.5 Stereo JACK

Maximum output level : 1Vrms

Use built-in amplifier when connecting to speakers.

| PIN No. | Signal | Schematic |
|---------|-----------|-----------|
| 1 | SG | |
| 2 | Lineout R | |
| 3 | Lineout L | |

4-8-7 Audio Interface (MIC IN)

Interface : MIC IN (Mono)

Connector : ϕ 3.5 Stereo JACK

Maximum input level : 250mVrms

| PIN No. | Signal | Schematic |
|---------|--------|-----------|
| 1 | SG | |
| 2 | NC *1 | |
| 3 | MIC | |

*1. NC is 'not connected'.

4-8-8 Power Connector

Interface : 24VDC IN

Connector : Euro terminal connector (<Tyco Electronics>284539-3)

Recommended cable connector : (<Tyco Electronics>284510-3) *Included as accessory.

| PIN No. | Signal | Schematic |
|---------|--------|-----------|
| 1 | FG | |
| 2 | GND | |
| 3 | +24VDC | |

4-9 Software Specification

The EMG7 line up is Embedded Linux.

4-9-1 Embedded Linux

The following tool is recommended for application software development.

- Qt

Linux Specifications

| Item | Specifications | |
|--------------------|--------------------|--|
| Glibc Version | 2.23 | |
| Installed software | Qt5.7.1 | GUI Tool kit |
| | PCMan File Manager | File manager |
| | uim | Japanese input method |
| | anthy | Conversion engine |
| | GTK+ | GIMP Toolkit library |
| | bash | Bash shell |
| | busybox | The program stored Linux basic command |
| | udhcp | DHCP Client |
| | gdbserver | gdb debugger connected from host |
| | ntpclient | Sync time by NTP |
| | Lighttpd | Web Server (php,cg supported) |
| | x11 | X Window System |
| | x11vnc | VNC Server/Client |
| | LXTerminal | Terminal emulator |
| | ALSA | Audio mixer |
| | emg-setting | EMG setting tool |
| | florence | Screen keyboard |
| | leafpad | Text editor |
| | evince | PDF viewer |
| openssh | SSH server | |
| libmodbus | Modbus library | |

*For details, please refer to the EM series software

In the EMG7 embedded Linux version, it is possible to install our InfoSOSA as an HMI application.


To use as InfoSOSA, please purchase the development kit.

For details of InfoSOSA please refer to the InfoSOSA Reference Manual.


5. Installation

5-1 Installing Condition

- When mounting the EMG7 to panels, be sure to have enough room for inserting and removing SD cards, cables, and mounting brackets.
- Be sure that the ambient operation temperature (0°C to 55°C) and the ambient humidity (10%RH to 85%RH. Wet-bulb temperature is 39 °C or less) are within their designated ranges.
- “Ambient operation temperature” indicates both the display side and inside of cabinet where the EMG7 will be installed.




- EMG7 should be mounted perpendicular, but if it should be mounted in an angle, the angle shall not be more than 30 degrees from the vertical position shown in the illustration below:



- When installing the EMG7 in a slanted panel of angle 30 degrees or more, please use forced air cooling to ensure the temperature specification.


5-2 Mounting

5-2-1 Panel Mounting



The EMG7 may be mounted in panels of thickness 1.0mm to 5.0mm

Panel cut dimension is as shown below:



The material of the mounting panel, please use the metal.

Be recommended panel thickness range, depending on material and size, may not maintain the strength when an impact is applied.

Please do take into account, such as reinforcement in the environment impact, such as join.

There is a possibility of personal injury or product damage when dropped product,


Please be careful not to drop.

5-2-2 Mounting to a VESA Arm

EM can be installed on a commercially available Video Electronics Standards Association (VESA) MIS-D arm, stand, or apparatus that is listed to comply with the UL1678 standard.

Refer to manual of arm or stand for installation procedures.

Mounting hole dimension is as below.



Use M4 screws to mount.

The tightening torque range is 0.7 to 0.8Nm.

M4 screws used should be 6mm or less in length

6. Compatible Standards

EMG is intended for use in industrial environments and, when properly installed, shall comply with the following agency approvals.

6-1 UL Standard

This product is UL standard compliant

| UL standard No. | UL Registration Model No. | UL File No. |
|--|---------------------------|-------------|
| UL 61010-1 / UL 61010-2-201 CSA C22.2 No 142-M1987; | G-0001UA | E464360 |

6-2 CE Marking

This product is EMC Directive of EU compliant

Complying standard : EMI:EN 61000-6-4:2007+AI:2011
EMS:EN 61000-6-2:2005

6-3 RoHS Directives

This product is RoHS Directive of EU compliant.

6-4 FCC

The FCC requires the following note to be published according to FCC guidelines:

Note:

This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user is required to correct the interference at their own expense. Changes or modifications to this unit that are not expressly approved by DMC could void the user's authority to operate the equipment.

Industry Canada requires the following note to be published:

Note:

This Class A digital apparatus complies with Canadian CAN ICES-3 (A)/NMB-3 (A).

7. List of Option

■ Mounting brackets

| Model | Description |
|----------|-------------|
| IS-TK-01 | 4pcs |

■ Development kit

| Model | Description |
|----------|---|
| SWDK-101 | Power supply unit Software development environment (DVD) |

*The option for EMG7-W207A8-0024-107-01 (Linux Model)

This is needed when using InfoSOSA application.

8. Warranty

8-1 Warranty Period

The warranty period is limited to 12 months (1 year) from the date of shipment. Warranty for any repair needed to the same repaired part of the same product is three months. Any defects that occur upon normal use under conditions specified herein will be repaired (factory repair) free of charge.

Any defected parts under proper use will be examined by the supplier and replaced by the new parts if the defect is considered to be caused by the supplier.

The replacement is subject to be included in the next lot.

8-2 Warranty Exceptions

You will be liable for all repair fees even within the warranty period for any conditions listed below:

- (1) Any malfunctions, defects, and/or damages that occurred during transport, transfer, or mishandling by the user after delivery.
- (2) Any malfunctions, defects, and/or damages caused by natural or man-made disaster.
- (3) Any malfunctions and damages caused by static electricity.
- (4) If the product is used under any condition, in any environment, or by any method other than those specified in the specifications, catalogs, manuals, notes, and/or other documents.
- (5) Any replacement of consumables.
- (6) Any malfunctions, defects, and/or damages caused by associated equipment and/or usage of inappropriate consumables and media.
- (7) If the product is repaired, remodeled, modified, or disassembled by a party other than DMC.
- (8) If the product cannot be identified by a serial number.
- (9) Any malfunctions, defects, and/or damages that are to have been caused on your behalf.

This warranty covers only the product itself. Any damages, on-site repairs and replacement driven by the failure of the product will be decided upon discussion by both parties as necessary.

This product is structurally not repairable. All damaged parts are subject for replacement and freight will be charged.

9. Production Discontinuance

In the event of product discontinuance, an announcement will be made on our website six months prior to the last possible order reception date.

10. Others

If you have comments or questions, please feel free to contact us.

North South America area

✉ technical-global@dush.co.jp

Asia Pacific area

✉ technical-global-asia@dush.co.jp

Europe, Middle East, Africa area

✉ technical-global-eu@dush.co.jp

FAQ

 www.dush.co.jp/english/support/faq/

11th Edition April 2024

DMC Co., Ltd.

Office hours: 9:00 - 17:00 weekdays (JST)

(except Saturdays, Sundays, national holidays, and year-end and New Year holidays)



URL: <https://www.dush.co.jp/english/>

This product and document are protected by the copyright law.

Photocopying, duplicating, reproducing, and modifying of this product or document in part or by whole is prohibited.

Copyright(C) 2024 DMC Co., Ltd. All Rights Reserved

| 寸法許容差 TOLERANCE | |
|----------------------------|-------|
| 呼び寸法 Nominal Dimensions | |
| L ≤ 3 | ±0.4 |
| 3 < L ≤ 6 | ±0.48 |
| 6 < L ≤ 10 | ±0.58 |
| 10 < L ≤ 18 | ±0.7 |
| 18 < L ≤ 30 | ±0.84 |
| 30 < L ≤ 50 | ±1.0 |
| 50 < L ≤ 80 | ±1.2 |
| 80 < L ≤ 120 | ±1.4 |
| 120 < L ≤ 180 | ±1.6 |
| 180 < L ≤ 250 | ±1.85 |
| 250 < L ≤ 315 | ±2.1 |
| 315 < L ≤ 400 | ±2.3 |
| 400 < L ≤ 500 | ±2.5 |





パネル開口寸法 (S=1:5)
Panel Cutout Dimensions (S=1:5)



| SYM | 改訂日 DATE | 改訂内容 DESCRIPTION | ページ PAGE | 担当 DESIGNED |
|-----|-------------|--|-------------|----------------|
| | 2016.09.01 | 新規図面登録 New Diagram Registration | - | S. Yoshimoto |
| △ | 2023.04.18 | 表題欄社名変更 Company name change in title block. | - | S. Takada |

NOTES

- 誤動作の恐れがある為、パネル開口寸法をお守り下さい。
又、取付けパネルには、反り、傷、凹凸のないものを使用して下さい。
To prevent malfunctions, panel opening dimension shall strictly be as specified.
Be sure to use installation panels without warpage, scratches, and dents.



状態表示LED
Status Display LED




4-M4
ネジ 侵入深さ6mm以下
Effective Screw Depth 6mm

ライセンスシール
License Label

FCCラベル
FCC Label

製品銘板シール
Product Label



電源インターフェイス
Power input

ネットワークインターフェイス
Ethernet

シリアルインターフェイス
Serial port

USBホストインターフェイス
USB host port

NOTES

- 指示なき寸法公差は一般寸法公差とする。
Tolerance shall be of general dimensional tolerance unless specified otherwise.

| | | | | | | | |
|----------------|------------|----------------|-----------------|---------------|-------------------------|------------------------------|---------------------------|
| 製図日 ISSUED | 2023.04.18 | 部署 SECTION | Technical Dept. | 尺度 SCALE | CAD登録名 CAD FILE NAME | 11K015-4_EMG7-W207A8_OUTLINE | RoHS対応品 RoHS compliant |
| 承認 APPROVED | | 検図 CHECKED | | 1:2 | 製品名 MODEL | EMG7-W207A8-0024-XXX-01 | |
| | | 製図 DRAWN | S. Takada | 単位 UNIT | 図名 TITLE | OUTLINE | ページ PAGE |
| | | 設計 DESIGNED | S. Takada | mm | | | 1 / 1 |
| T. Okada | | S. Yoshimoto | | DMC Co., Ltd. | | A3 | |
| | | | | 図番 DWG No. | | SM3-001905-11 | |